



### Overview

Description	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Model Name	APC IT Power Distribution Module 3 Pole 4 Wire 60A IEC309 560cm
Includes	Installation guide
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Canada

### Output

Nominal Output Voltage	208 3PH
Maximum Total Current Draw per Phase	60 A
Output Connections	(1) IEC 309 60A (3P+PE) (Battery Backup)

### Input

Nominal Input Voltage	208 3PH
Input Frequency	60 Hz
Acceptable Input Voltage	200-240 VAC
Maximum Line Current per phase	60 A

### Physical

Net Weight	10.6 lbs (4.82 kg)
Maximum Height	5.0 inches (127.0 mm)
Maximum Width	17.5 inches (445.0 mm)
Maximum Depth	16.0 inches (406.0 mm)
Shipping Weight	11.8 lbs (5.36 kg)
Shipping Height	5.0 inches (127.0 mm)
Shipping Width	17.5 inches (445.0 mm)
Shipping Depth	16.0 inches (406.0 mm)

Conformance

---

Approvals	UL Listed
Standard warranty	1 year repair or replace

---

Sustainable Offer Status

---

RoHS	Compliant
------	-----------

---