



Overview

| | |
|----------------------|--|
| Description | Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time. |
| Model Name | APC IT Power Distribution Module 3 Pole 4 Wire 60A IEC309 620cm |
| Includes | Installation guide |
| Standard Lead Time | Usually Ships within 3 Weeks |
| Product Distribution | Canada , Japan , United States |

Output

| | |
|--------------------------------------|--|
| Nominal Output Voltage | 208 3PH |
| Maximum Total Current Draw per Phase | 60 A |
| Output Connections | (1) IEC 309 60A (3P+PE) (Battery Backup) |

Input

| | |
|--------------------------------|-------------|
| Nominal Input Voltage | 208 3PH |
| Input Frequency | 60 Hz |
| Acceptable Input Voltage | 200-240 VAC |
| Maximum Line Current per phase | 60 A |

Physical

| | |
|-----------------|------------------------|
| Net Weight | 11.0 lbs (5.0 kg) |
| Maximum Height | 5.0 inches (127.0 mm) |
| Maximum Width | 17.5 inches (445.0 mm) |
| Maximum Depth | 16.0 inches (406.0 mm) |
| Shipping Weight | 12.2 lbs (5.55 kg) |
| Shipping Height | 5.0 inches (127.0 mm) |
| Shipping Width | 17.5 inches (445.0 mm) |
| Shipping Depth | 16.0 inches (406.0 mm) |

Conformance

| | |
|-------------------|--------------------------|
| Approvals | UL Listed |
| Standard warranty | 1 year repair or replace |

Sustainable Offer Status

| | |
|------|-----------|
| RoHS | Compliant |
|------|-----------|
