



### Overview

Description	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Model Name	APC IT Power Distribution Module 3 Pole 5 Wire 20A 240V IEC309 980cm
Includes	Installation guide
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Canada , Japan , United States

### Output

Nominal Output Voltage	240V
Maximum Total Current Draw per Phase	20 A
Output Connections	(1) IEC 309 (Battery Backup)

### Input

Nominal Input Voltage	230V
Input Frequency	60 Hz
Input Connections	IEC 309
Acceptable Input Voltage	200-240 VAC
Maximum Line Current per phase	20 A

### Physical

Net Weight	13.4 lbs (6.09 kg)
Maximum Height	5.0 inches (127.0 mm)
Maximum Width	17.5 inches (444.0 mm)
Maximum Depth	16.0 inches (406.0 mm)
Shipping Weight	14.6 lbs (6.64 kg)
Shipping Height	5.0 inches (127.0 mm)
Shipping Width	17.5 inches (444.0 mm)
Shipping Depth	16.0 inches (406.0 mm)

Conformance

---

Approvals	UL Listed
Standard warranty	1 year repair or replace

---

Sustainable Offer Status

---

RoHS	Compliant
------	-----------

---