



Overview

Description	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Model Name	APC IT Power Distribution Module 3 Pole 5 Wire 30A L21-30 800cm
Includes	Installation guide
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Canada

Output

Nominal Output Voltage	120V
Maximum Total Current Draw per Phase	30 A
Output Connections	(1) NEMA L21-30 (Battery Backup)

Input

Nominal Input Voltage	208 3PH
Input Frequency	60 Hz
Acceptable Input Voltage	200-240 VAC
Maximum Line Current per phase	30 A

Physical

Net Weight	12.2 lbs (5.55 kg)
Maximum Height	5.0 inches (127.0 mm)
Maximum Width	17.5 inches (445.0 mm)
Maximum Depth	16.0 inches (406.0 mm)
Shipping Weight	13.4 lbs (6.09 kg)
Shipping Height	5.0 inches (127.0 mm)
Shipping Width	17.5 inches (445.0 mm)
Shipping Depth	16.0 inches (406.0 mm)

Conformance

Approvals	UL Listed
Standard warranty	1 year repair or replace

Sustainable Offer Status

RoHS	Compliant
------	-----------
