



Overview

Model Name	32' CABLE EXTENDER 5-WIRE #10 AWG, UL WITH L21-20R/P
Includes	Installation guide
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Anguilla

Output

Nominal Output Voltage	120V
Maximum Total Current Draw per Phase	20 A

Input

Nominal Input Voltage	208 3PH
Input Connections	NEMA L21-20P
Number of Power Cords	1
Acceptable Input Voltage	200-240 VAC
Maximum Line Current per phase	20 A

Physical

Net Weight	10.3 lbs (4.68 kg)
Maximum Height	2.5 inches (64.0 mm)
Maximum Width	2.0 inches (51.0 mm)
Maximum Depth	384.0 inches (9754.0 mm)
Shipping Weight	10.9 lbs (4.95 kg)
Shipping Height	4.0 inches (102.0 mm)
Shipping Width	12.0 inches (305.0 mm)
Shipping Depth	17.5 inches (445.0 mm)
Color	Black

Conformance

Approvals	UL Listed
-----------	-----------

Standard warranty

2 years repair or replace
