



### Overview

Model Name	3 Wire Cord w/L6-30 5 ft
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Canada , United States

### Output

Nominal Output Voltage	208V
Output Connections	(1) NEMA L6-30R (Battery Backup)

### Input

Nominal Input Voltage	208V
Input Connections	Hard Wire 3-wire
Cord Length	5 feet (1.52 meters)
Number of Power Cords	1
Maximum Line Current per phase	30 A

### Physical

Net Weight	4.42 lbs (2.02 kg)
Maximum Height	4.0 inches (102.0 mm)
Maximum Width	8.0 inches (203.0 mm)
Maximum Depth	8.0 inches (203.0 mm)
Shipping Weight	5.0 lbs (2.28 kg)
Shipping Height	6.0 inches (152.0 mm)
Shipping Width	12.0 inches (305.0 mm)
Shipping Depth	12.0 inches (305.0 mm)
Color	Black

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications