



Overview

Model Name	RDP INPUT CORD & CONNECTOR SET - 8 FOOT
Includes	Installation guide
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guadeloupe , Guatemala , Guyana , Haiti , Honduras , Jamaica , Martinique , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , Turks And Caicos Islands , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Nominal Output Voltage	208V
Maximum Total Current Draw per Phase	80 A
Output Connections	(1) IEC 309 32A (Battery Backup)
Cord Length	8

Input

Nominal Input Voltage	208V
Input Connections	IEC 309
Number of Power Cords	1
Acceptable Input Voltage	200-240 VAC
Maximum Line Current per phase	80 A

Physical

Net Weight	29.2 lbs (13.28 kg)
Maximum Height	5.0 inches (127.0 mm)
Maximum Width	24.0 inches (610.0 mm)
Maximum Depth	96.0 inches (2438.0 mm)
Shipping Weight	32.71 lbs (14.86 kg)
Shipping Height	11.42 inches (290.0 mm)
Shipping Width	25.2 inches (640.0 mm)

Shipping Depth	25.2 inches (640.0 mm)
----------------	------------------------

Conformance

Standard warranty	2 years repair or replace
-------------------	---------------------------
