

PE6U21W

APC SurgeArrest Essential Multi-Use 6 Outlet
with 2 Type-A 1 Type-C Port 4.8A USB Charger
White 120V



Overview

Model Name	APC SurgeArrest Essential Multi-Use 6 Outlet with 2 Type-A 1 Type-C Port 4.8A USB Charger White 120V
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla

Output

Number of Outlets	6
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	6 feet (1.83 meters)
Maximum Input Current	15 A

Surge Protection and Filtering

Surge energy rating	1080 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	40.0 dB
Peak Current Normal Mode	24 kA
Peak Current Common Mode	48.0 kA
NM Surge Response Time (ns)	1.0 NS
Let Through Voltage Rating	500

Physical

Net Weight	1.52 lbs (0.69 kg)
Maximum Height	5.31 inches (135.0 mm)

Maximum Width	2.72 inches (69.0 mm)
Maximum Depth	5.2 inches (132.0 mm)
Shipping Weight	1.7 lbs (0.77 kg)
Shipping Height	5.43 inches (138.0 mm)
Shipping Width	4.72 inches (120.0 mm)
Shipping Depth	6.73 inches (171.0 mm)
Master Carton Units	6.0
Master Carton Dimensions (Length x Width x Height)	16.14 x 12.52 x 7.48 inches
Master Carton Weight	5.48 kg
SCC Codes	1073130434372 8
Units per Pallet	192.0

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	FCC Part 15 Class B
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$50000

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs