


PER8TR

APC PERSONAL SURGEARREST 8 OUTLET W/ TEL 120V RETAIL



PER8TR has not been replaced. Please contact your customer care center for more information.

Overview

Model Name	APC PERSONAL SURGEARREST 8 OUTLET W/TEL 120V RETAIL
Includes	1.8 Meter Tel cable (2) , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Canada , Mexico , United States

Output

Number of Outlets	8
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A

Surge Protection and Filtering

EMI/RFI Noise rejection (100 kHz to 10 MHz)	50.0 dB
Peak Current Normal Mode	17.5 kA
Peak Current Common Mode	32.0 kA
Data Line Protection	RJ-11 Modem/Fax protection
Let Through Voltage Rating	330

Physical

Net Weight	1.57 lbs (0.71 kg)
Maximum Height	9.75 inches (248.0 mm)
Maximum Width	3.75 inches (96.0 mm)
Maximum Depth	1.25 inches (32.0 mm)
Shipping Weight	2.0 lbs (0.91 kg)
Shipping Height	15.75 inches (401.0 mm)
Shipping Width	11.25 inches (286.0 mm)

Shipping Depth	3.0 inches (77.0 mm)
SCC Codes	10731304187308

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	CSA , FCC Part 68 , UL 1363 , UL 1449 , UL 497A
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$50000
UL 1449 TVSS Rating	330
