

Product data sheet

Characteristics


PFA32060GN

60A 120/208V F-Frame Circuit Breaker Busway Plug-In Unit

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,640.00 USD



Main

Product or component type	Section
Module type	F-Frame

Complementary

Fixing mode	Plug-in
System Voltage	208 V AC 120 V AC
[Ie] rated operational current	60 A
Busbar description	Ground
Disconnecter device type	Thermal magnetic circuit breaker : 60 A

Environment

Product certifications	CSA UL
------------------------	-----------

Ordering and shipping details

Category	20181 - PFA 240V C/B PLUGS
Discount Schedule	PE7
GTIN	00785901018391
Nbr. of units in pkg.	1
Package weight(Lbs)	18.5
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant
------------------------	-----------

Jun 19, 2019

 Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------