

# Product data sheet

## Characteristics

# PFA34050GN

## Busway I-Line Circuit Breaker Plug-in Unit, 50A, FA Frame, 480V, 4 Wire

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 1,978.00 USD



### Main

Product or component type	Plug-in unit
Range of product	I-Line
Circuit breaker type	FA
Trip unit technology	Thermal-magnetic

### Complementary

Protection type	Circuit breaker
Mounting mode	Plug-in
Line Rated Current	50 A
System Voltage	277/480 V AC
Phase	3 phases
Poles description	3P
Wiring configuration	4-wire (integral ground bus)
Interrupt Rating	18 kA at 480 V AC 25 kA at 240 V AC
AWG gauge	AWG 10...AWG 2 1 cable(s) ground AWG 14...AWG 1/0 1 cable(s) phase and neutral
Depth	8.62 in (219 mm)
Height	8.27 in (210 mm)
Width	14.37 in (365 mm)

### Environment

Product certifications	UL listed file E22182 CSA C22.2 No 27
Standards	UL 857

## Ordering and shipping details

Category	20182 - PFA / PHD C/B PLUGS
Discount Schedule	PE7
GTIN	00785901022220
Nbr. of units in pkg.	1
Package weight(Lbs)	18.5
Returnability	Y
Country of origin	US

## Offer Sustainability

RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------