

Product data sheet

Characteristics

PFA34060GN

Busway I-Line Circuit Breaker Plug-in Unit, 60A,
FA Frame, 480V, 4 Wire

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,978.00 USD

PFA34060GN has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

Main

Product or component type	Plug-in unit
Range of product	I-Line
Circuit breaker type	FA
Trip unit technology	Thermal-magnetic

Complementary

Protection type	Circuit breaker
Mounting mode	Plug-in
Line Rated Current	60 A
System Voltage	277/480 V AC
Poles description	3P
Phase	3 phases
Wiring configuration	4-wire (integral ground bus)
Interrupt Rating	18 kA at 480 V AC 25 kA at 240 V AC
AWG gauge	AWG 10...AWG 2 1 cable(s) ground AWG 14...AWG 1/0 1 cable(s) phase and neutral
Height	8.27 in (210 mm)
Depth	8.62 in (219 mm)
Width	14.37 in (365 mm)

Environment

Product certifications	UL listed file E22182 CSA C22.2 No 27
Standards	UL 857

Ordering and shipping details

Category	20182 - PFA / PHD C/B PLUGS
Discount Schedule	PE7
GTIN	00785901022237
Nbr. of units in pkg.	1
Package weight(Lbs)	18.5
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1438 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------