



Overview

Model Name	Prefabricated Power Module 750kW 480V/60Hz with Galaxy VX
Includes	User Manual
Standard Lead Time	Special Order - Call for Quoted Lead Times
Product Distribution	Canada

Output

Configured Power	750000
Max Configurable Power (Watts)	750.0 KW / 750.0 kVA
Nominal Output Voltage	480 3PH

Input

Input Frequency	60 Hz - programmable +/- 0.5 / 1 / 2 / 4 / 6 / 8%
-----------------	---

Batteries & Runtime

Battery Type	VRLA
--------------	------

Physical

Maximum Height	120.0 inches (3048.0 mm)
Maximum Width	118.2 inches (3002.0 mm)
Maximum Depth	54.0 inches (1371.6 mm)
Net Weight	70000.0 lbs (31751.44 kg)
Shipping Weight	48000.0 lbs (21772.42 kg)
Shipping Height	124.0 inches (3150.0 mm)
Shipping Width	120.0 inches (3048.0 mm)
Shipping Depth	54.8 inches (1391.9 mm)

Environmental

Audible noise at 1 meter from surface of unit	0.000 dB
---	----------