



### Main

Product or component type	Circuit breaker
Range of product	PowerPact P
Current sensor rating range	400 A
Line Rated Current	400 A
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
Trip unit technology	Electronic ammeter Micrologic 3.0 A LI

### Complementary

Product certifications	UL listed CSA IEC
System Voltage	600 V AC
Module type	P-Frame
Mounting location	Busbar
Mounting mode	Unit mount
Poles description	3P
Breaking capacity code	G
Electrical connection	Busbar connection load Busbar connection line
Continuous current rating	80 %
Device short name	A
Height	12.86 in
Depth	8.05 in
Width	8.27 in
Tightening torque	50 N.mFor 0.15...0.37 in <sup>2</sup> (95...240 mm <sup>2</sup> ) (AWG 3/0...500 kcmil) 1...1.3 N.m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications