

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 32,100.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact P
Current sensor rating range	600 A
Line Rated Current	600 A
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
AWG gauge	AWG 3/0...500 kcmil aluminium/copper 3(cable(s))
Trip unit technology	Electronic harmonic Micrologic 6.0 H LSIG

### Complementary

Product certifications	UL listed IEC CSA
System Voltage	600 V AC
Module type	P-Frame
Mounting location	Bolt-on
Mounting mode	Unit mount
Poles description	3P
Breaking capacity code	G
Electrical connection	Lugs load Lugs line
Continuous current rating	100 %
Device short name	A
Communication interface	Modbus
Height	12.86 in
Depth	8.05 in
Width	8.27 in
Tightening torque	50 N.mFor 0.15...0.37 in <sup>2</sup> (95...240 mm <sup>2</sup> ) (AWG 3/0...500 kcmil)

### Ordering and shipping details

Category	01215 - PG,H,J,K,L,N UNIT MT BREAKERS
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	32
Returnability	Y
Country of origin	US

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------