

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 28,476.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact P
Current sensor rating range	800 A
Line Rated Current	800 A
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
AWG gauge	AWG 3/0...500 kcmil aluminium/copper 3(cable(s))
Trip unit technology	Electronic power Micrologic 6.0 P LSIG

Complementary

Product certifications	IEC CSA UL listed
System Voltage	600 V AC
Module type	P-Frame
Mounting location	Bolt-on
Mounting mode	Unit mount
Poles description	3P
Breaking capacity code	G
Electrical connection	Lugs load Lugs line
Continuous current rating	100 %
Device short name	A
Communication interface	Modbus
Height	12.86 in
Depth	8.05 in
Width	8.27 in
Tightening torque	50 N.mFor 0.15...0.37 in ² (95...240 mm ²) (AWG 3/0...500 kcmil)

Ordering and shipping details

Category	01215 - PG,H,J,K,L,N UNIT MT BREAKERS
Discount Schedule	DE2
GTIN	00785901974277
Nbr. of units in pkg.	1
Package weight(Lbs)	32
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------