

# PH8U2W

APC Home Office SurgeArrest 8 Outlets with 2 USB Charging Ports (5V, 2.4A in total), 120V White



## Overview

Model Name	APC Home Office SurgeArrest 8 Outlets with 2 USB Charging Ports (5V, 2.4A in total), 120V White
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

## Output

Number of Outlets	6
Receptacle Style	NEMA 5-15R

## Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	6 feet (1.83 meters)
Maximum Input Current	15 A

## Surge Protection and Filtering

Surge energy rating	2160 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	40.0 dB
Peak Current Normal Mode	28 kA
Peak Current Common Mode	56.0 kA
NM Surge Response Time (ns)	1.0 NS
Let Through Voltage Rating	400

## Physical

Net Weight	1.48 lbs (0.67 kg)
Maximum Height	1.18 inches (30.0 mm)
Maximum Width	3.05 inches (77.0 mm)
Maximum Depth	11.69 inches (297.0 mm)
Shipping Weight	1.71 lbs (0.78 kg)
Shipping Height	1.89 inches (48.0 mm)
Shipping Width	5.71 inches (145.0 mm)
Shipping Depth	13.19 inches (335.0 mm)
Master Carton Units	6.0
Master Carton Dimensions (Length x Width x Height)	13.78 x 6.3 x 12.6 inches
Master Carton Weight	5.03 kg
SCC Codes	1073130433620 1
Color	White
Units per Pallet	324.0

## Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-50000 feet (0-15000 meters)

## Conformance

Approvals	FCC Part 15 Class B , MET Canada , MET USA , UL 1363 , UL 1449 , UL 60950-1
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$150000

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs