



Main

Product or component type	Circuit breaker
Range of product	PowerPact P
Current sensor rating range	250 A
Line Rated Current	250 A
Breaking capacity	100 kA 240 V AC 65 kA 480 V AC 25 kA 600 V AC
Trip unit technology	Electronic harmonic Micrologic 6.0 H LSIG

Complementary

Product certifications	CSA IEC UL listed
System Voltage	600 V AC
Module type	P-Frame
Mounting location	Busbar
Mounting mode	Unit mount
Poles description	3P
Breaking capacity code	J
Electrical connection	Busbar connection load Busbar connection line
Continuous current rating	100 %
Device short name	A
Communication interface	Modbus
Height	12.86 in
Depth	8.05 in
Width	8.27 in
Tightening torque	50 N.mFor 0.15...0.37 in ² (95...240 mm ²) (AWG 3/0...500 kcmil) 1...1.3 N.m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.