Product data sheet

Specifications



Automatic switch, PowerPacT P, 600A, 3 pole, 600VAC, 25kA, lugs, magnetic, black rotary handle

PJL36000S60RE10

Discontinued on: Jul 20, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Product Or Component Type | Automatic switch |
|--------------------------------|------------------|
| Range Of Product | PowerPact P |
| Trip Unit Technology | Magnetic |
| Accessory / Separate Part Type | Rotary handle |

Complementary

| Complementary | |
|--------------------------------|---|
| Line Rated Current | 600 A |
| [Ue] Rated Operational Voltage | 600 V AC |
| Mounting Mode | Unit mount |
| Poles Description | 3P |
| Short-Circuit Withstand | 65 kA 480 V UL 489 25 kA 600 V UL 489 100 kA 240 V UL 489 |
| Breaking Capacity Code | J |
| Electrical Connection | Lugs, line Lugs, load |
| Awg Gauge | 3 x AWG 3/0500 kcmil (aluminium/copper) |
| Terminal Identifier | AL800M23K |
| Magnetic Tripping Current | 10000 A |
| Height | 16.24 in (412.50 mm) |
| Width | 16.54 in (420.12 mm) |
| Depth | 14.49 in (368.05 mm) |
| Tightening Torque | 442.54 lbf.in (50 N.m) 0.150.37 in ² (95240 mm ²) (AWG 3/0500 kcmil) |

Environment

Product Certifications

IEC CSA UL Listed

Ordering and shipping details

| Category | US10DE201215 |
|-------------------|--------------|
| Discount Schedule | 0DE2 |
| Gtin | 785901655275 |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Returnability | No |
|-------------------|----|
| Country Of Origin | US |

Packing Units

| - | |
|------------------------------|----------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 12.50 in (31.75 cm) |
| Package 1 Width | 12.00 in (30.48 cm) |
| Package 1 Length | 20.60 in (52.324 cm) |
| Package 1 Weight | 38.84 lb(US) (17.618 kg) |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 24 |
| Package 2 Height | 36.00 in (91.44 cm) |
| Package 2 Width | 40.00 in (101.6 cm) |
| Package 2 Length | 48.00 in (121.92 cm) |
| Package 2 Weight | 934.00 lb(US) (423.655 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |