





PowerPact

PowerPact P

Circuit breaker

Circuit breaker, PowerPacT P, 600A, 3 pole, 600VAC, 25kA, lugs, Micrologic 5.0H, 100%, modbus

PJL36060CU73AE1

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 33,104.00 USD

Main Range

Product Name

Product Or Component Type

[Ui] Rated Insulation Voltage

Accessory / Separate Part Type

Trip Unit Name

Awg Gauge

Local Signalling

Mounting Mode

Mounting Support

Electrical Connection

C. Call S. Calles
Distribution
600 A
3P
Toggle
J
AIR 100 kA 240 V AC 50/60 Hz UL 489 AIR 65 kA 480 V AC 50/60 Hz UL 489 AIR 25 kA 600 V AC 50/60 Hz UL 489 Icu 65 kA 240 V AC 50/60 Hz IEC 60947-2 Icu 50 kA 380/415 V AC 50/60 Hz IEC 60947-2
600 V AC 50/60 Hz UL 489
50/60 Hz
35 kA 240 V AC 50/60 Hz IEC 60947-2 25 kA 380/415 V AC 50/60 Hz IEC 60947-2
8 kV IEC 60947-2
Electronic, harmonic, MicroLogic 5.0 H, LSI
100 %

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

750 V IEC 60947-2

MicroLogic 5.0 H

Unit mount lug)

Lug

Lugs, line Lugs, load

Modbus connecting cable

Overload 1 trip indicator green) 1 trip indicator green)

Trip causes 1 trip indicator green)

3 x AWG 3/0...500 kcmil aluminium/copper

Terminal Identifier	AL800M23K
Long Time Pick-Up Adjustment Range	0.41 x lr
Tightening Torque	442.54 lbf.in (50 N.m) 0.150.37 in² (95240 mm²) (3 x AWG 3/0500 kcmil) 8.8511.51 lbf.in (1.01.3 N.m)
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)
Power Wire Stripping Length	0.98 in (25 mm)
Height	12.86 in (326.64 mm)
Width	8.27 in (210.06 mm)
Depth	8.05 in (204.47 mm)
Net Weight	32 lb(US) (14.51 kg)
Quantity Per Set	1
Communication Interface	Modbus
Circuit Breaker Application	HACR rated

Environment

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover IP40
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	28158 °F (-270 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating 13123.36 ft (4000 m) with derating

Ordering and shipping details

Category	US10DE201215
Discount Schedule	0DE2
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.75 in (29.845 cm)
Package 1 Width	11.63 in (29.528 cm)
Package 1 Length	20.25 in (51.435 cm)

Package 1 Weight

32.00 lb(US) (14.515 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
②	Rohs Exemption Information	Yes
Ø	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov