

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 14,595.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact P
Current sensor rating range	800 A
Line Rated Current	800 A
Breaking capacity	125 kA 240 V AC 100 kA 480 V AC
AWG gauge	AWG 3/0...500 kcmil aluminium/copper 3(cable(s))
Trip unit technology	Electronic basic ET 1.0I LI

Complementary

Product certifications	CSA IEC UL listed
System Voltage	480 V AC
Module type	P-Frame
Mounting location	Bolt-on
Mounting mode	Unit mount
Poles description	2P
Breaking capacity code	L
Electrical connection	Lugs load Lugs line
Continuous current rating	80 %
Height	12.86 in
Depth	8.05 in
Width	8.27 in
Tightening torque	50 N.mFor 0.15...0.37 in ² (95...240 mm ²) (AWG 3/0...500 kcmil) 1...1.3 N.m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	01215 - PG,H,J,K,L,N UNIT MT BREAKERS
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	32
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------