

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 15,660.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact P
Current sensor rating range	800 A
Line Rated Current	800 A
Breaking capacity	25 kA 600 V AC 125 kA 240 V AC 100 kA 480 V AC
AWG gauge	AWG 3/0...500 kcmil aluminium/copper 3(cable(s))
Trip unit technology	Electronic basic ET 1.0I LI

Complementary

Product certifications	CSA UL listed IEC
System Voltage	480 V AC
Module type	P-Frame
Mounting location	Bolt-on
Mounting mode	Unit mount
Poles description	3P
Breaking capacity code	L
Electrical connection	Terminal nut line Lugs load
Height	12.86 in
Depth	8.05 in
Width	8.27 in
Tightening torque	50 N.mFor 0.15...0.37 in ² (95...240 mm ²) (AWG 3/0...500 kcmil) 1...1.3 N.m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	01215 - PG,H,J,K,L,N UNIT MT BREAKERS
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	32
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------