

PNETR6

APC Surge Module for CAT6 or CAT5/5e Network Line, Replaceable, 1U, use with PRM4 or PRM24 Chassis



Overview

| | |
|----------------------|--|
| Description | Protects an ethernet data port from damaging transients. Supports Cat5, Cat5E and Cat6 cabling standards. Compatible with Power Over Ethernet (POE) and network speeds up to 10GbE (10GigE). |
| Model Name | APC Surge Module for CAT6 or CAT5/5e Network Line, Replaceable, 1U, use with PRM4 or PRM24 Chassis |
| Includes | User Manual |
| Standard Lead Time | Usually in Stock |
| Product Distribution | Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahamas , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominica , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Grenada , Guadeloupe , Guatemala , Guinea , Guyana , Haiti , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Romania , Russian Federation , Rwanda , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe |

Output

| | |
|-------------------|---|
| Number of Outlets | 1 |
|-------------------|---|

Surge Protection and Filtering

| | |
|--------------------------|---|
| Peak Current Normal Mode | 0.2 kA |
| Peak Current Common Mode | 0.25 kA |
| Data Line Protection | RJ45 10/100/1000 Base-T Ethernet protection |

Physical

| | |
|--|-----------------------------|
| Net Weight | 0.04 lbs (0.02 kg) |
| Maximum Height | 1.72 inches (44.0 mm) |
| Maximum Width | 0.74 inches (19.0 mm) |
| Maximum Depth | 2.72 inches (69.0 mm) |
| Shipping Weight | 0.1 lbs (0.04 kg) |
| Shipping Height | 3.9 inches (99.0 mm) |
| Shipping Width | 1.3 inches (33.0 mm) |
| Shipping Depth | 3.76 inches (95.0 mm) |
| Master Carton Units | 96.0 |
| Master Carton Dimensions (Length x Width x Height) | 25.12 x 16.25 x 8.13 inches |
| Master Carton Weight | 6.01 kg |
| SCC Codes | 3073130421718 4 |
| Color | Black |

Environmental

| | |
|-----------------------------|------------------------------|
| Operating Environment | 5 - 113 °F (-15 - 45 °C) |
| Operating Relative Humidity | 0 - 95 % |
| Operating Elevation | 0-10000 feet (0-3000 meters) |
| Storage Temperature | 5 - 113 °F (-15 - 45 °C) |
| Storage Relative Humidity | 0 - 95 % |
| Storage Elevation | 0-10000 feet (0-3000 meters) |

Conformance

| | |
|-------------------|-------------------------|
| Approvals | UL 497B , UL Recognized |
| Standard warranty | Lifetime |

Sustainable Offer Status

| | |
|------|-----------|
| RoHS | Compliant |
|------|-----------|
