

PTMJ36300GV

Busway I-Line Circuit Breaker Plug-in Unit, 300A,
M-Frame, 25kA-600V, 3W, Vert

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 17,918.00 USD



Main

Product or component type	Plug-in unit
Range of product	I-Line
Circuit breaker type	M-frame
Trip unit technology	Electronic, basic, ET 1.0, LI

Complementary

Protection type	Circuit breaker
Mounting mode	Bolt-on
Line Rated Current	300 A
System Voltage	600 V AC
Phase	3 phases
Poles description	3P
[Ics] rated service short-circuit breaking capacity	80 %
Wiring configuration	3-wire (integral ground bus)
Interrupt Rating	65 kA at 480 V AC 25 kA at 600 V AC 100 kA at 240 V AC
AWG gauge	AWG 3/0...500 kcmil 3 cable(s) phase and neutral AWG 6...300 kcmil 4 cable(s) ground
Depth	514 mm
Height	1174 mm
Width	584 mm
Condition of use	Vertical installation

Environment

Product certifications	UL listed file E22182
------------------------	-----------------------

Standards	UL 857
-----------	--------

Ordering and shipping details

Category	20192 - PBMH/PTMH C/B PLUGS
Discount Schedule	PE7
Nbr. of units in pkg.	1
Package weight(Lbs)	284
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
