

# Product data sheet

Specifications



Automatic switch, PowerPacT Q,  
225A, 2 pole, 480VAC, lugs,  
magnetic

QBL22000S22

Product availability: Non-Stock - Not normally stocked in  
distribution facility

Price\*: 660.00 USD

## Main

Product Or Component Type	Automatic switch
Range Of Product	PowerPacT Q
Trip Unit Technology	Magnetic
Circuit Breaker Type	Q-Frame

## Complementary

Line Rated Current	225 A
[Ue] Rated Operational Voltage	240 V AC
Mounting Mode	Unit mount
Poles Description	2P
Short-Circuit Withstand	10 kA 240 V UL 489
Breaking Capacity Code	B
Electrical Connection	Lugs, line Lugs, load
Awg Gauge	x AWG 4...300 kcmil ( aluminium/copper )
Magnetic Tripping Current	4500 A
Height	16.24 in (412.50 mm)
Width	16.54 in (420.12 mm)
Depth	14.49 in (368.05 mm)
Tightening Torque	247.82 lbf.in (28 N.m) 0.04...0.23 in² (25...150 mm²) (AWG 4...300 kcmil)

## Environment

Product Certifications	IEC UL Listed CSA
------------------------	-------------------------

## Ordering and shipping details

Category	US1DE2A00005
Discount Schedule	DE2A
Gtin	785901901655
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.56 in (14.127 cm)
Package 1 Width	5.81 in (14.757 cm)
Package 1 Length	9.75 in (24.765 cm)
Package 1 Weight	3.36 lb(US) (1.525 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™** label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 Rohs Exemption Information   [Yes](#)

 Pvc Free

 Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>