

# Product data sheet

## Characteristics

# QBL22090

PowerPact Q - molded case circuit breaker - 2-pole - 10 kA - 240 V - 90 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 474.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

### Complementary

Line Rated Current	90 A
System Voltage	240 V AC
Number of poles	2
Breaking capacity	10 kA 240 V AC
Continuous current rating	80 %
Breaking capacity code	B
Mounting mode	Unit mount
Electrical connection	Lugs load AWG 4...300 kcmil aluminium/copper Lugs line AWG 4...300 kcmil aluminium/copper
Magnetic hold current	1000 A
Magnetic tripping current	1800 A
Height	6.47 in
Width	4.5 in
Depth	3.93 in
Tightening torque	28 N.mFor 25...150 mm <sup>2</sup> (AWG 4...300 kcmil)

### Environment

Product certifications	IEC CSA UL listed
------------------------	-------------------------

## Ordering and shipping details

Category	00005 - QO,Q2L 2P ENCL & BREAKERS
Discount Schedule	DE2A
GTIN	00785901407584
Nbr. of units in pkg.	1
Package weight(Lbs)	3.4100000000000001
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1413 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------