

Product data sheet

Characteristics

QBL22225

PowerPact Q - molded case circuit breaker - 2-pole - 10 kA - 240 V - 225 A

Product availability : Stock - Normally stocked in distribution facility



Price* : 474.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

Complementary

Line Rated Current	225 A
System Voltage	240 V AC
Number of poles	2
Breaking capacity	10 kA 240 V AC
Continuous current rating	80 %
Breaking capacity code	B
Mounting mode	Unit mount
Electrical connection	Lugs load AWG 4...300 kcmil aluminium/copper Lugs line AWG 4...300 kcmil aluminium/copper
Magnetic hold current	1200 A
Magnetic tripping current	2400 A
Height	6.47 in
Width	4.5 in
Depth	3.93 in
Tightening torque	28 N.mFor 25...150 mm ² (AWG 4...300 kcmil)

Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

Ordering and shipping details

Category	00005 - QO,Q2L 2P ENCL & BREAKERS
Discount Schedule	DE2A
GTIN	00785901412663
Nbr. of units in pkg.	1
Package weight(Lbs)	3.3700000000000001
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1413 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------