

Product data sheet

Characteristics

QBP32200TP

PowerPact Q - molded case circuit breaker - 3-pole - 10 kA - 208Y/120 V - 200 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,248.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

Complementary

Line Rated Current	200 A
System Voltage	208Y/120 V AC
Number of poles	3
Breaking capacity	10 kA 240 V AC
Continuous current rating	80 %
Breaking capacity code	B
Mounting mode	Unit mount
Electrical connection	Terminal nut line AWG 4...300 kcmil aluminium/copper Lugs load
Magnetic hold current	1200 A
Magnetic tripping current	2400 A
Height	6.47 in
Width	4.5 in
Depth	3.93 in

Environment

Product certifications	UL listed IEC CSA
------------------------	-------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	00187 - Q2M REPL MAIN CB
Discount Schedule	DE2A
GTIN	00785901546719
Nbr. of units in pkg.	1
Package weight(Lbs)	4.5300000000000002
Returnability	N
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------