

Product availability : Stock - Normally stocked in distribution facility



Price\* : 1,562.00 USD



### Main

Product or component type	Meter Mains
Range of product	QO

### Complementary

Line Rated Current	200 A
Short-circuit current	22 kA
Network number of phases	1
Meter socket type	Ringless
Mounting	Surface
Number of spaces	0
Number of circuits	0
Mounting	Surface
Number of Tandem Breakers	0
Hub type	A
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 6...350 kcmil (aluminium/copper) line side AWG 12...AWG 2/0 (aluminium/copper) service ground
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	200 A
Service feed location	OH UG
Bypass type	No bypass
Depth	6.1 in
Width	14.89 in
Height	26.16 in

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Product certifications	UL E-6294
------------------------	-----------

## Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901001126
Nbr. of units in pkg.	1
Package weight(Lbs)	40.369999999999997
Returnability	Y
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0944 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------