

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 1,905.00 USD



Main

Product or component type	All-In-One
Range of product	QO
Meter socket type	Ringless
Hub type	A

Complementary

Line Rated Current	200 A
Short-circuit current	22 kA
Mounting	Surface
Number of spaces	24
Number of circuits	42
Number of Tandem Breakers	18
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 6...350 kcmil (aluminium) line side AWG 6...350 kcmil (copper) line side AWG 8...AWG 2/0 (aluminium) service ground AWG 8...AWG 2/0 (copper) service ground
Disconnect	Service disconnect (factory installed)
Disconnect Rating	200 A
Branch Breaker Rating	200 A
Service feed location	OH UG
Bypass type	Horn bypass

Ordering and shipping details

Category	00122 - QO CSED DEVICES
Discount Schedule	DE3A

GTIN	00785901396789
Nbr. of units in pkg.	1
Package weight(Lbs)	43.719999999999999
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0944 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------