

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,356.00 USD



Main

Product or component type	Meter Mains
Range of product	QO

Complementary

Line Rated Current	100 A
Short-circuit current	22 kA
Network number of phases	1
Meter socket type	Ringless
Mounting	Surface
Number of spaces	8
Number of circuits	16
Mounting	Surface
Number of Tandem Breakers	8
Hub type	A
Electrical connection	Lugs line side Feed-thru lugs service ground
Wire Size	AWG 6...350 kcmil (aluminium/copper) line side AWG 12...AWG 2/0 (aluminium/copper) service ground
Disconnect	Service disconnect (factory installed)
Main Breaker Rating	100 A
Branch Breaker Rating	100 A
Service feed location	OH UG
Bypass type	Horn bypass
Depth	5.07 in
Width	14 in
Height	35.15 in

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Product certifications	UL E-6294
------------------------	-----------

Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901401803
Nbr. of units in pkg.	1
Package weight(Lbs)	10
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0944 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------