

# Product data sheet

## Characteristics

# QC816F150SS

## METERMAIN RINGLESS OH/UG 150A

### SURFACESOLAR

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 1,507.00 USD



### Main

Product or component type	Meter Mains
Range of product	QO
Includes	Circuit breaker 1 2P pole 150 A, 120/240 V AC, main supply ready assembled

### Complementary

Line Rated Current	150 A
Short-circuit current	22 kA
Network number of phases	1
Meter socket type	Ringless
Mounting	Surface outdoor
Number of spaces	8
Number of circuits	16
Number of Tandem Breakers	8
Hub type	A
Electrical connection	Feed-thru lugs line side Feed-thru lugs service ground
Wire Size	AWG 8...AWG 2/0 (aluminium/copper) service ground 350 kcmil (aluminium/copper) line side
Disconnect	Service disconnect (factory installed)
Main Breaker Rating	150 A
Branch Breaker Rating	150 A
Service feed location	OH UG
Bypass type	No bypass
Depth	5.41 in
Width	18.76 in
Height	41.16 in

## Environment

Product certifications	UL E-6294
------------------------	-----------

## Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901891550
Nbr. of units in pkg.	1
Package weight(Lbs)	65
Returnability	N

## Offer Sustainability

RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------