

Product data sheet

Characteristics

QDA221504

PowerPact Q - molded case circuit breaker - 2-pole - 25 kA - 240 V - 150 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,202.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

Complementary

Line Rated Current	150 A
System Voltage	240 V AC
Number of poles	2
Breaking capacity	25 kA 240 V AC
Continuous current rating	80 %
Breaking capacity code	D
Mounting mode	I-Line
Electrical connection	Lugs load AWG 4...300 kcmil aluminium/copper I-Line connection line BC
Phase connection	BA
Magnetic hold current	1200 A
Magnetic tripping current	2400 A
Height	6.47 in
Width	4.5 in
Depth	3.93 in
Tightening torque	28 N.mFor 25...100 mm ² (AWG 4...300 kcmil)

Environment

Product certifications	CSA UL listed IEC
------------------------	-------------------------

Ordering and shipping details

Category	01023 - Q2 BREAKER & SWITCH
Discount Schedule	DE2
GTIN	00785901485421
Nbr. of units in pkg.	1
Package weight(Lbs)	4.6299999999999999
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1413 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------