

# Product data sheet

## Characteristics

# QDA221755

PowerPact Q - molded case circuit breaker - 2-pole - 25 kA - 240 V - 175 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 1,202.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

### Complementary

Line Rated Current	175 A
System Voltage	240 V AC
Number of poles	2
Breaking capacity	25 kA 240 V AC
Continuous current rating	80 %
Breaking capacity code	D
Mounting mode	I-Line
Electrical connection	Lugs load AWG 4...300 kcmil aluminium/copper I-Line connection line CA
Phase connection	CA
Magnetic hold current	1200 A
Magnetic tripping current	2400 A
Height	6.47 in
Width	4.5 in
Depth	3.93 in

### Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

## Ordering and shipping details

Category	01023 - Q2 BREAKER & SWITCH
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	4.719999999999998
Returnability	Y
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------