





Circuit breaker, PowerPacT Q, 200A, 3 pole, 240VAC, 25kA, lugs, thermal magnetic, 80%, top of panel

QDM32200TN

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1,784.00 USD

#### Main

Range	PowerPact
Product Name	PowerPact Q
Product Or Component Type	Circuit breaker
Device Application	Distribution

## Complementary

Line Rated Current	200 A
Number Of Poles	3P
Control Type	Operating handle
Breaking Capacity Code	D
Breaking Capacity	25 kA 120/208 V AC 50/60 Hz UL 25 kA 240 V AC 50/60 Hz UL
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz UL
Network Frequency	50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV UL
Trip Unit Technology	Thermal-magnetic
Magnetic Tripping Current	2400 A
Magnetic Hold Current	1200 A
Continuous Current Rating	80 %
Utilisation Category	Category A
Mechanical Durability	1000 cycles loaded 5000 cycles no load
Local Signalling	1 trip indicator green)
Mounting Mode	Unit mount lug)
Mounting Support	Lug
Electrical Connection	Lugs, line Terminal nut, load
Tightening Torque	247.82 lbf.in (28 N.m) 0.040.23 in² (25150 mm²) (AWG 4300 kcmil)
Power Wire Stripping Length	0.87 in (22 mm)
Height	6.47 in (164.34 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	4.5 in (114.30 mm)
Depth	3.93 in (99.82 mm)
Circuit Breaker Application	HACR rated

## **Environment**

Standards	UL CSA NEMA NOM-003-SCFI-2000
Product Certifications	UL CSA NOM
Ambient Air Temperature For Operation	104158 °F (4070 °C)

# Ordering and shipping details

Category	US1DE2A00187	
Discount Schedule	nt Schedule DE2A	
Gtin	785901417309	
Returnability	Yes	
Country Of Origin	MX	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.98 in (15.2 cm)
Package 1 Width	6.10 in (15.5 cm)
Package 1 Length	9.88 in (25.1 cm)
Package 1 Weight	4.65 lb(US) (2.11 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>②</b>	Pvc Free	
<b>⊘</b>	Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov