

Product data sheet

Characteristics

QGA221103

PowerPact Q - molded case circuit breaker - 2-pole - 65 kA - 240 V - 110 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,593.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

Complementary

Line Rated Current	110 A
System Voltage	240 V AC
Number of poles	2
Breaking capacity	65 kA 240 V AC
Continuous current rating	80 %
Breaking capacity code	G
Mounting mode	I-Line
Electrical connection	Lugs load AWG 4...300 kcmil aluminium/copper I-Line connection line BA
Phase connection	BA
Magnetic hold current	1200 A
Magnetic tripping current	2400 A
Height	6.47 in
Width	4.5 in
Depth	3.93 in

Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

Ordering and shipping details

Category	01023 - Q2 BREAKER & SWITCH
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	5
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------