

Product data sheet

Specifications



Mini circuit breaker, QO, 15A, 3 pole, 120/240VAC, 65kA, plug in, AC shunt

QH3151021

⚠ Discontinued on: Jul 30, 2020

⚠ End-of-service on: Sep 22, 2020

⚠ Discontinued

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate
Options	Shunt trip 120/208/240 V AC

Complementary

Interrupt Rating	65 kA 120/240 V AC 65 kA 240 V AC 65 kA 120 V AC
Number Of Panel Spaces	4
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	2.99 in (76 mm)
Width	2.99 in (76 mm)
Depth	2.91 in (74 mm)
Net Weight	1.20 lb(US) (0.544 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00926-QO IND SPECIALTY CB
Discount Schedule	DE2A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.20 in (8.128 cm)
Package 1 Width	3.70 in (9.398 cm)
Package 1 Length	4.60 in (11.684 cm)
Package 1 Weight	19.20 oz (544.311 g)

Contractual warranty

Warranty	18 months
----------	-----------