

Product data sheet

Characteristics

QH325

Mini CB, QO, 25 A, 3P, 120/240 V, 65 kA, Plug in

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 507.00 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	25 A
System Voltage	120 V AC 120/240 V AC 240 V AC
Mounting Type	Plug-in
Number of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate

Complementary

Interruption Rating	65 kA at: 120/240 V AC 50/60 Hz 65 kA at: 120 V AC 50/60 Hz 65 kA at: 240 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	2.25 in

Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00926 - QO IND SPECIALTY CB
Discount Schedule	DE2A
GTIN	00785901362364
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8499999999999998
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------