

# Product data sheet

## Characteristics

# QHB1151021

## Mini CB, QO, 15 A, 1P, 120/240 V, 65 kA, Bolt on, Shunt Trip

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 311.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	15 A
System Voltage	120 V AC 120/240 V AC
Mounting Type	Bolt-on
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR and Switching Duty rated
Electrical Connection	Pressure plate
Options	Shunt trip, 120/208/240 V AC,

### Complementary

Interrupt Rating	65 kA at: 120/240 V AC 50/60 Hz 65 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	1.5 in

### Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901637752
Nbr. of units in pkg.	1
Package weight(Lbs)	0.670000000000000004
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------