

# Product data sheet

Specifications

SQUARE D



Mini circuit breaker, QO, 30A, 1 pole, 120/240VAC, 65kA, bolt on, 50 deg C, fungal treatment

QHB13035FT

⚠ Discontinued on: Dec 8, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	30 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Bolt-on
Number Of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate

## Complementary

Interrupt Rating	65 kA 120/240 V AC 65 kA 120 V AC
Number Of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	2.99 in (76 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.31 lb(US) (0.141 kg)

## Environment

Certifications	UL Listed CSA
Ambient Rating	122 °F (50 °C)

## Ordering and shipping details

Category	00015-QOB CIRCUIT BREAKERS
Discount Schedule	DE2
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.70 in (1.778 cm)
Package 1 Width	3.30 in (8.382 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	4.96 oz (140.614 g)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability




**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Compliant with Exemptions
China Rohs Regulation		<a href="#">China RoHS declaration</a>
		Product out of China RoHS scope. Substance declaration for your information.