

Product data sheet

Characteristics

QHB3301021

Mini CB, QO, 30 A, 3P, 120/240 V, 65 kA, Bolt on, Shunt Trip

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 785.00 USD



Main

| | |
|-----------------------|--------------------------------------|
| Product | Miniature circuit-breaker |
| Range | QO |
| Line Rated Current | 30 A |
| System Voltage | 120 V AC 120/240 V AC 240 V AC |
| Mounting Type | Bolt-on |
| Number of Poles | 3P |
| Circuit Breaker Type | Standard |
| Ratings | HACR rated |
| Electrical Connection | Pressure plate |
| Options | Shunt trip, 120/208/240 V AC, |

Complementary

| | |
|------------------------|---|
| Interrupt Rating | 65 kA at: 120/240 V AC 50/60 Hz 65 kA at: 120 V AC 50/60 Hz 65 kA at: 240 V AC 50/60 Hz |
| Number of Panel Spaces | 4 |
| Wire Size | AWG 14...AWG 8 (copper or aluminium) |
| Height | 3 in |
| Depth | 2.91 in |
| Width | 3 in |

Environment

| | |
|----------------|------------------|
| Certifications | CSA UL listed |
| Ambient Rating | 104 °F (40 °C) |

Ordering and shipping details

| | |
|-----------------------|------------------------------|
| Category | 00015 - QOB CIRCUIT BREAKERS |
| Discount Schedule | DE2 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1.8500000000000001 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant Schneider Electric declaration of conformity |
| REACH | Reference contains SVHC above the threshold Go to CaP for more details |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|