

Product data sheet

Characteristics

QJA220802

PowerPact Q - molded case circuit breaker - 2-pole - 100 kA - 240 V - 80 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,992.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

Complementary

Line Rated Current	80 A
System Voltage	240 V AC
Number of poles	2
Breaking capacity	100 kA 240 V AC
Continuous current rating	80 %
Breaking capacity code	J
Mounting mode	I-Line
Electrical connection	Lugs load AWG 4...300 kcmil aluminium/copper I-Line connection line AC
Phase connection	AC
Magnetic hold current	1000 A
Magnetic tripping current	1800 A
Height	6.47 in
Width	4.5 in
Depth	3.93 in

Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

Ordering and shipping details

Category	01023 - Q2 BREAKER & SWITCH
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	4.54
Returnability	Y
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------