

# Product data sheet

## Characteristics

# QJL22250

PowerPact Q - molded case circuit breaker - 2-pole - 100 kA - 240 V - 250 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 2,348.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

### Complementary

Line Rated Current	250 A
System Voltage	240 V AC
Number of poles	2
Breaking capacity	100 kA 240 V AC
Continuous current rating	80 %
Breaking capacity code	J
Mounting mode	Unit mount
Electrical connection	Lugs line AWG 4...300 kcmil copper Lugs load AWG 4...300 kcmil copper
Magnetic hold current	1200 A
Magnetic tripping current	2400 A
Height	6.47 in
Width	4.5 in
Depth	3.93 in
Tightening torque	28 N.mFor 25...150 mm <sup>2</sup> (AWG 4...300 kcmil)

### Environment

Product certifications	IEC UL listed CSA
------------------------	-------------------------

**Ordering and shipping details**

Category	00005 - QO,Q2L 2P ENCL & BREAKERS
Discount Schedule	DE2A
Nbr. of units in pkg.	1
Package weight(Lbs)	3.3500000000000001
Returnability	Y
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
------------------------	--

**Contractual warranty**

Warranty period	18 months
-----------------	-----------