

Product data sheet

Characteristics

QJL32250

PowerPact Q - molded case circuit breaker - 3-pole - 100 kA - 208Y/120 V - 250 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 3,465.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

Complementary

Line Rated Current	250 A
System Voltage	208Y/120 V AC
Number of poles	3
Breaking capacity	100 kA 208Y/120 V AC
Continuous current rating	80 %
Breaking capacity code	J
Mounting mode	Unit mount
Electrical connection	Lugs line AWG 4...300 kcmil copper Lugs load AWG 4...300 kcmil copper
Magnetic hold current	1200 A
Magnetic tripping current	2400 A
Height	6.47 in
Width	4.5 in
Depth	3.93 in
Tightening torque	28 N.mFor 25...150 mm ² (AWG 4...300 kcmil)

Environment

Product certifications	IEC UL listed CSA
------------------------	-------------------------

Ordering and shipping details

Category	00023 - QO,Q2L 3P ENCL & BREAKERS
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	4.7400000000000002
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------