

Product data sheet

Characteristics

QJP32175TM

PowerPact Q - molded case circuit breaker - 3-pole - 100 kA - 240 V - 175 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 2,796.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic
Provided equipment	Lug OFF end Stud with nut and washer ON end

Complementary

Line Rated Current	175 A
System Voltage	208Y/120 V AC
Number of poles	3
Breaking capacity	100 kA 208Y/120 V AC
Continuous current rating	80 %
Breaking capacity code	J
Mounting mode	Unit mount
Electrical connection	Lugs load AWG 4...300 kcmil aluminium/copper Terminal nut line
Magnetic hold current	1200 A
Magnetic tripping current	2400 A
Height	6.47 in
Width	4.5 in
Depth	3.93 in
Tightening torque	28 N.mFor 25...150 mm ² (AWG 4...300 kcmil)

Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

Ordering and shipping details

Category	00024 - Q2 & QE METERING BREAKERS
Discount Schedule	DE2A
GTIN	00785901686477
Nbr. of units in pkg.	1
Package weight(Lbs)	4
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------