

Product data sheet

Characteristics

QMB1IMA16

Surge Protect - QMB - IMA - 160kA - 120/240VAC - 1P3W

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 7,340.00 USD



Main

Product	Surge protection device
Range	QMB
Device Short Name	IMA

Complementary

Surge Current	160 kA
System Voltage	120/240 V AC
Phase	1 phase
Wiring Configuration	3-wire
Connection	Plug in
MCOV	150 V
Nominal Discharge Current	20 kA
SCCR	200 kA
Local Signalling	Alarm = fault Status LED
Provided Equipment	Surge counter Alarm enable/disable switch Dry contacts
Height	22.99 in (584 mm)
Width	8.9 in (226 mm)
Depth	6.5 in (165 mm)

Environment

Enclosure Material	Painted sheet steel
--------------------	---------------------

Ordering and shipping details

Category	08251 - TVSS UNIT
Discount Schedule	PE1A
Nbr. of units in pkg.	1
Package weight(Lbs)	37
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------