

Product data sheet

Characteristics

QMB261TW

30A-30A 4.5 Inch 2P 600VAC/250VDC Fusible Switch

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 1,050.00 USD



Main

Product or component type	Fuse-switch disconnecter
Number of poles	2
[Ue] rated operational voltage	600 V AC 250 V DC
Line Rated Current	30 A - 30 A 600 V AC
Fuse type	R

Complementary

Height	4.49 in (114 mm)
Number of modules	2

Environment

Product certifications	CSA UL
------------------------	-----------

Ordering and shipping details

Category	00037 - QMB BRANCH CB,SW,& MAIN SW
Discount Schedule	PE1A
GTIN	00785901748045
Package weight(Lbs)	7.63 kg (16.82 lb(US))
Returnability	No
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------