

Product data sheet

Characteristics

QMB2IMA24

Surge Protect - QMB - IMA - 240kA -
208Y/120VAC - 3P4W - UL - CSA

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 10,460.00 USD



Main

Product	Surge protection device
Range	QMB
Device Short Name	IMA

Complementary

Surge Current	240 kA
System Voltage	208Y/120 V AC
Phase	3 phases
Wiring Configuration	4-wire
Connection	Plug in
MCOV	150 V
Nominal Discharge Current	20 kA
SCCR	200 kA
Local Signalling	Alarm = fault Status LED
Provided Equipment	Surge counter Alarm enable/disable switch Dry contacts
Height	8.9 in (226 mm)
Width	584 mm
Depth	6.5 in (165 mm)

Environment

Enclosure Material	Painted sheet steel
Standards	UL 1283 CSA C22.2 No 8 1986 UL 1449 ed. 3

Ordering and shipping details

Category	08251 - TVSS UNIT
Discount Schedule	PE1A
Nbr. of units in pkg.	1
Package weight(Lbs)	40
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016 Will be compliant on 4Q2016
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------