

# Product data sheet

## Characteristics

# QO1101200

Mini CB, QO, 10 A, 1P, 120/240 V, 10 kA, Plug in, Aux Switch 1A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 161.00 USD



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	10 A
System Voltage	120 V AC 120/240 V AC 48 V DC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	Not rated
Electrical Connection	Pressure plate
Options	Auxiliary switch, 120 V AC, 1A contact(s)

### Complementary

Interrupt Rating	5 kA at: 48 V DC 10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	1.5 in

### Environment

Certifications	CSA UL listed
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00004 - QO,QOT 10-30A 1P;10-60A 2P
Discount Schedule	DE2A
Nbr. of units in pkg.	1
Package weight(Lbs)	0.01
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------