

Product data sheet

Characteristics

QO11035

Mini CB, QO, 10 A, 1P, 120/240 V, 10 kA, Plug in, 50Deg

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 35.00 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	10 A
System Voltage	120 V AC 120/240 V AC 48 V DC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	Not rated
Electrical Connection	Pressure plate

Complementary

Interrupt Rating	5 kA at: 48 V DC 10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	0.75 in

Environment

Certifications	CSA UL listed
Ambient Rating	122 °F (50 °C)

Ordering and shipping details

Category	00080 - QO SPECIALTY CB,1&2 POLE
Discount Schedule	DE2A
Nbr. of units in pkg.	1
Package weight(Lbs)	0.32000000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------